

## LUXASCOPE DERMATOSCOPE LED 2.5 V - CONTACT PLATE WITH SCALE - LUXAMED ®

**LUXAMED®**

Ref. C1.516.934



**+ Graduation**




 13/03/2025 23:09:36 - For information purposes only, can be subject to change

GSH | 30 rue Jean de Guiramand  
13290 Aix-en-Provence | France

 [www.gsh-med.fr](http://www.gsh-med.fr)

 +33(0)4 42 90 31 31

 [info@gsh-med.fr](mailto:info@gsh-med.fr)

## LUXASCOPE DERMATOSCOPE LED 2.5 V - CONTACT PLATE WITH SCALE - LUXAMED ®

**LUXAMED®**

**Ref. C1.516.934**

Innovative pocket-sized dermatoscope with graduated contact plate.

Available in a range of colours.

### Description

- Lighting: LED ring with 6 (concentric) LEDs, for a highly detailed image and even lighting.
- Maintenance-free, as no bulb change is required.
- Removable contact plate for easy cleaning
- Continuous zoom with X10 magnification for a distortion-free image
- Optimised head design
- Brightness can be dimmed to avoid glare
- Automatic switch-off after 3 minutes
- LED life: approx. 100,000 hours at constant current
- Illuminance: approx. 10,000 Lux
- Colour temperature: approx. 4,200 K
- Handle made of two materials: aluminium and reinforced fibreglass, compatible with the head of the Luxascope CCT otoscope and ophthalmoscope
- ON/OFF push-button switch
- Power supply: 2x AAA alkaline batteries, included

Available in :

- White: C1.516.914
- Light blue: C1.516.934
- Yellow: C1.516.944
- Fuchsia: C1.516.974
- Yellow : C1.516.944
- Kids : C1.916.914
- Black : C1.516.114



13/03/2025 23:09:36 - For information purposes only, can be subject to change

Green : C1.516.954

GSH | 30 rue Jean de Guiramand  
13290 Aix-en-Provence | France

[www.gsh-med.fr](http://www.gsh-med.fr)

+33(0)4 42 90 31 31

[info@gsh-med.fr](mailto:info@gsh-med.fr)

Bar code	04260381963738	HS Code	90189084
Warranty (months)	24	Country	Germany
DIMENSIONS AND WEIGHT			
Packed unit / Width (cm)	nc	Packed unit / Height (cm)	nc
Packed unit / Length (cm)	nc	Packed unit / Weight	nc
SPECIFIC STORAGE CONDITIONS			
Minimum temperature	5	Max temperature	40
Minimum humidity	10	Maximum humidity	90
OTHER FEATURES			
Colors	Light blue		