


MOBI WITH ADULT ARMBAND (M) SPENGLER, 4 COLORS TO CHOOSE FROM

Ref. 513702



CE
0459



22/01/2026 21:15:32 – For information purposes only, can be subject to change

MOBI WITH ADULT ARMBAND (M) SPENGLER, 4 COLORS TO CHOOSE FROM



Ref. 513702

Elegant and colorful, the MOBI blood pressure monitor revolutionizes the aneroid blood pressure monitor thanks to its new patented connectors.

Description

The "LIFE LINK®" tubing allows the cuff to be changed in less than a second thanks to its magnetic connectors that ensure the connection and sealing between the pressure gauge and the tubing.

- AMBIDEXTRE : Mobi is specially designed to be ambidextrous, choose your configuration and change the position of the decompression valve, the "LIFE LINK®" connectors and the spoon.

- ERGONOMIC PEAR: The ergonomic pear is suitable for all hand morphologies and offers a volume gain of 11% on traditional pears.

- PRECISION VALVE: MOBI is equipped with a decompression valve whose shape is studied to offer the best sensitivity during decompression but also a very good ergonomics and grip.

- SHOCK RESISTANT: Due to its ABS plastic construction, its double inner shell and its elastomer rear part, MOBI is specially designed to offer great resistance to shocks and falls in everyday life.

- EASY ARMBAND with the revolutionary "LIFE LINK®" connectors, designed in TPU coating to be lighter and easy to clean.

-
COLORED: Mobi exists in 4 colors: Carbon, Blueberry, Coral and Powder Pink-

Comes with an M cuff and a LIFE LINK® tubing

- Optional: 5 sizes of armbands (XS, S, M, L, XL)

MOBI WITH ADULT ARMBAND (M) SPENGLER, 4 COLORS TO CHOOSE FROM



Ref. 513702

Features

CE Marking	CE0459	Medical device	Class Im (measuring function)
Bar code	3700446027971	HS Code	90189010
Warranty (months)	36	Country	China
DIMENSIONS AND WEIGHT			
Packed unit / Width (cm)	nc	Packed unit / Height (cm)	nc
Packed unit / Length (cm)	nc	Packed unit / Weight	0.52
SPECIFIC STORAGE CONDITIONS			
Minimum temperature	-20	Max temperature	70
Minimum humidity	20	Maximum humidity	85
OTHER FEATURES			
Colors	Carbon		