

# LUXASCOPE AURIS LED 2.5 V - LUXAMED

Ref. A1.416.954

**LUXAMED®**



CE



28/01/2026 22:36:37 – For information purposes only, can be subject to change

## LUXASCOPE AURIS LED 2.5 V - LUXAMED

Ref. A1.416.954

**LUXAMED®**

Innovative otoscope in pocket size

### Description

Illumination: LED-Ring with 6 LEDs (concentric),  
no fibre optic, field of vision is not restricted

- Maintenance-free, because no lamp replacement necessary
- Can be dimmed
- Automatic switchoff after 3 minutes
- Life expectancy of LEDs: approx. 100.000 hours  
by constant current drive
- Intensity of illumination: approx. 10.000 Lux
- Colour temperature: approx. 4.200 K
- Optimized design of head
- Pivoting 3-fold magnifying glass with locking function
- Insufflation port for pneumatic test
- Two-component handle (aluminium / fibre-glass reinforced),  
also combinable with LuxaScope LED Dermatoscope- and  
Ophthalmoscope head
- Electronic ON/OFF push-button switch
- Power supply: 2x AAA Alkaline batteries, inclusive
- Incl. 20 disposable ear funnels, grey,  
each 10 x 2.5 mm and 10 x 4.0 mm

# LUXASCOPE AURIS LED 2.5 V - LUXAMED

Ref. A1.416.954

**LUXAMED®**

## Features

|                                    |                |                           |            |
|------------------------------------|----------------|---------------------------|------------|
| CE Marking                         | CE             | Medical device            | Class I    |
| Bar code                           | 04260381963936 | HS Code                   | 9018908400 |
| Warranty (months)                  | 24             | Country                   | Germany    |
| <b>DIMENSIONS AND WEIGHT</b>       |                |                           |            |
| Packed unit / Width (cm)           | 11             | Packed unit / Height (cm) | 4          |
| Packed unit / Length (cm)          | 24             | Packed unit / Weight      | 0.3        |
| Bare Unit / Weight (kg)            | 0.12           |                           |            |
| <b>SPECIFIC STORAGE CONDITIONS</b> |                |                           |            |
| Minimum temperature                | 5              | Max temperature           | 40         |
| Minimum humidity                   | 10             | Maximum humidity          | 90         |
| <b>OTHER FEATURES</b>              |                |                           |            |
| Colors                             | Green          |                           |            |

📅 28/01/2026 22:36:37 – For information purposes only, can be subject to change