

LUXASCOPE AURIS SET LED 2.5 V, BLACK - OTOSCOPE + OPHTHALMOSCOPE

Ref. AF.416.114

LUXAMED®



CE



Complete set for precision diagnosis: Auris LED 2.5V black otoscope + LuxaScope LED 2.5V black ophthalmoscope

Description

Otoscope :

18/08/2026 13:30:47 – For information purposes only, can be subject to change

LUXASCOPE AURIS SET LED 2.5 V, BLACK - OTOSCOPE + OPHTHALMOSCOPE

LUXAMED®

Ref. AF.416.114

Lighting: LED ring with 6 LEDs (concentric),

no fibre optics, the field of vision is not limited.

- Maintenance-free, as no bulb change is required.
- Possibility of varying brightness intensity.
- Automatic switch-off after 3 minutes
- LED life: approx. 100,000 hours at constant current
current
- Illuminance: approx. 10,000 Lux
- Colour temperature: approx. 4,200 K
- Optimised head design
- Swivelling magnifier, 3x magnification
- Injection port for pneumatic test
- Handle made from two materials: aluminium and fibreglass
fibreglass, compatible with the head of the Lux dermatoscope and
LuxaScope ophthalmoscope head
- ON/OFF push-button switch
- Power supply: 2x AAA alkaline batteries, included
- Includes 20 grey disposable specula, 10 of which are 2.5mm and 10 of which are
4.0mm specula

Ophthalmoscope :

- Correction values: + 20 bis - 20 D ($\pm$ 1 2 3 4 6 8 10 15 20 D)
- 5 different filters available: large spot, small spot, green filter,
half-moon and reticle
- Illumination: LED
- Brightness can be dimmed to avoid glare

LUXASCOPE AURIS SET LED 2.5 V, BLACK - OTOSCOPE + OPHTHALMOSCOPE

LUXAMED®

Ref. AF.416.114

glare

- Automatic switch-off after 3 minutes
- LED life: approx. 50,000 hours at constant current

current

- Colour temperature: approx. 4,200 K
- Optimised head design
- Handle made from two materials: aluminium and fibreglass reinforced, compatible with otoscope and dermatoscope heads

LuxaScope LED

- ON/OFF push-button switch
- Includes 2 AAA alkaline batteries

Features

CE Marking	CE	Medical device	Class I
Bar code	04260381964438	HS Code	90189084
Warranty (months)	24	Country	Germany

DIMENSIONS AND WEIGHT

Packed unit / Width (cm)	nc	Packed unit / Height (cm)	nc
Packed unit / Length (cm)	nc	Packed unit / Weight	nc

SPECIFIC STORAGE CONDITIONS

Minimum temperature	-10	Max temperature	45
Minimum humidity	10	Maximum humidity	90

OTHER FEATURES