

## DIAGNOSTIC PENLIGHT LED - LUXAMED

Ref. D1.211.512

**LUXAMED®**



 18/08/2026 13:58:58 – For information purposes only, can be subject to change

## DIAGNOSTIC PENLIGHT LED - LUXAMED

Ref. D1.211.512

**LUXAMED®**

Diagnostic Penlight LED OF Luxamed is resistant and lasts over time thanks to LED technology!

This technology provides a shadow-free field of vision and optimum illumination in the area of application. The LEDs are powered by a constant current, guaranteeing considerably longer life.

### Description

Penlight for optimal eye and throat examinations, with LED light approved for eye examinations.

- Top quality ABS plastic housing
- Weight 31.5 g
- Life time LED 100.000 h
- Luminous intensity 18.000 – 22.000 mcd
- Colour temperature: approx. 7000 Kelvin
- Operating voltage 3.0 V
- Incl. 2 AAA batteries

Available in :

White (Ref : D1.211.912)

Blue (Ref : D1.211.212)

Grey (Ref : D1.211.312)

Yellow (Ref : D1.211.512)

Kids (Ref : D1.311.912)

Black (Ref : D1.211.112)

Red (Ref : D1.211.412)

Green (Ref : D1.211.612)

**DIAGNOSTIC PENLIGHT LED - LUXAMED**Ref. D1.211.512**LUXAMED®****Features**

|                   |                |                |          |
|-------------------|----------------|----------------|----------|
| CE Marking        | CE             | Medical device | Class I  |
| Bar code          | 04260381961727 | HS Code        | 90189084 |
| Warranty (months) | 24             | Country        | Germany  |

**DIMENSIONS AND WEIGHT**

|                           |      |                           |    |
|---------------------------|------|---------------------------|----|
| Packed unit / Width (cm)  | nc   | Packed unit / Height (cm) | nc |
| Packed unit / Length (cm) | nc   | Packed unit / Weight      | nc |
| Bare Unit / Weight (kg)   | 0.04 |                           |    |

**SPECIFIC STORAGE CONDITIONS**

|                     |     |                  |    |
|---------------------|-----|------------------|----|
| Minimum temperature | -10 | Max temperature  | 40 |
| Minimum humidity    | 10  | Maximum humidity | 90 |

**OTHER FEATURES**

|        |        |
|--------|--------|
| Colors | YELLOW |
|--------|--------|