




## SPENGLER - SMARTLED OTOSCOPE - BLACK

Ref. A1.416.112



09/09/2026 23:25:24 – For information purposes only, can be subject to change

## SPENGLER - SMARTLED OTOSCOPE - BLACK

Ref. A1.416.112



### SMARTLED SPENGLER X LUXAMED EDITION® OTOSCOPE

An innovative design otoscope made in Germany, tailored to the needs of healthcare professionals.

## Description

Key features :

Design and sturdiness:

- Lightweight (100gr), ideal for fatigue-free everyday use.
- Aluminium and fibreglass-reinforced handle
- Iconic Spengler colour

Bright illumination :

- Provides 10,000 Lux of brightness for clear observation.
- Colour temperature: 4,250 K

Technological innovation:

- Ring of 6 concentric LEDs positioned at the front for a clear, shadow-free field of vision
- Extended service life with constant current, approximately 100,000 hours.
- Adjustable brightness with a long press on the ON/OFF button
- Automatic switch-off after 3 minutes

Quality and innovation MADE IN GERMANY

Also available in Blueberry, Bronze and paediatric version (green)

Includes: 2 AAA/LR03 batteries + 20 disposable specula (10 in 2.5 mm and 10 in 4 mm)

# SPENGLER - SMARTLED OTOSCOPE - BLACK

Ref. A1.416.112



## Features

|                   |               |                |          |
|-------------------|---------------|----------------|----------|
| CE Marking        | CE            | Medical device | Class I  |
| Bar code          | 4260381965305 | HS Code        | 90189084 |
| Warranty (months) | 36            | Country        | Germany  |

### DIMENSIONS AND WEIGHT

|                           |      |                           |     |
|---------------------------|------|---------------------------|-----|
| Packed unit / Width (cm)  | 11   | Packed unit / Height (cm) | 4   |
| Packed unit / Length (cm) | 24   | Packed unit / Weight      | 0.3 |
| Bare Unit / Weight (kg)   | 0.12 |                           |     |

### SPECIFIC STORAGE CONDITIONS

|                     |    |                  |    |
|---------------------|----|------------------|----|
| Minimum temperature | 5  | Max temperature  | 40 |
| Minimum humidity    | 10 | Maximum humidity | 90 |

### OTHER FEATURES